Flush Lens (FL) shown. See page 6 for other lens details.

4"

[101.763mm]

Direct/Indirect performance as a single circuit or individual up/down control with two circuits.

High efficiency programmable driver for custom lumen packages. 0-10V dimming to 1% standard.



Bios SkyBlue™ circadian technology available.



Note DLC options at bottom of page.

# **Ordering Guide**

MODEL	OPTICS	CCT <sup>1</sup>	LUMENS4	LENGTH⁵	MOUNTING	FINISH	OPTIONS
PRFL-44-D							
PRFL-44-D Direct	FL = Flush Opal Acrylic (Standard snap-in) DL = Drop Opal Acrylic (snap-in) SI = Satin Ice Acrylic (lay-in) SIL = Satin Ice lens winternal Cross Baffle (white) SIL = Satin Ice w/ Internal Cross blade Louver (white) Direct Flush Lens shown. See page 6 for Drop and Lay-in Lens details.	STATIC WHITE¹ 27 = 2700K 30 = 3000K 35 = 3500K 40 = 4000K 50 = 5000K  BIOS SkyBlue² Spectrally optimized circadian solutions.  TUNABLE WHITE³ (2700K-6500K) 2DIM10 = for 0-10V 2DMX = for DMX 2PSQ = for Lutron 2ESN = for Philips 2CAS = for Casambi  RGB + WHITE³ RGB = RGB RGBW = RGBW  ADVANCED COLOR³ 125mm incremental pixel color control for chases and animated effects.	LO = 600/ft (5W/ft, 120LPW) SO = 800/ft (7W/ft, 118LPW) HO = 1000/ft (9W/ft, 117LPW) Consult factory for custom lumen pack- ages. All values nominal.	2 = 2 ft 3 = 3 ft 4 = 4 ft 5 = 5 ft 6 = 6 ft 7 = 7 ft 8 = 8 ft For other enter row length (e.g. 48 = 48 ft)	AC = Aircraft Cable PD = Pendant Stem S = Surface Mount	W = White CC = Custom Color AMW = Anti-Microbial White	DIMMING DRIVERS  DIM10 = 0-10V (1%) - Standard  DIMSR = 0-10V (5.0%) Sensor Ready  DIMST = Step Dimming (40%/100%)  DALI = DALI (5.0%)  LUTRON™ DIMMING DRIVERS  LDE1 = Hi-Lume™ 1% EcoSystem™  L3DA3W = Hi-Lume™ 1% 3-Wire  SENSORS & CONTROLS  ESN = Philips™ EasySense  DAY = Daylight Harvesting  OCC = Occupancy Sensor  CAS = Casambi Bluetooth control  VDO = Vive Sensor by Lutron  AWNR = Athena Wireless Node  AWNS = Athena Wireless Sensor  EMERGENCY  EMC = Emergency Circuit  GTD = Generator Transfer Device  EPC4 = 4W Emergency Battery Pack  EPC10 = 10W Emergency Battery Pack  EPC12 = 12W Emergency Battery Pack

<sup>&</sup>lt;sup>1</sup> CCT @ 80+CRI, 3SDCM. For 90CRI add prefix "9"; ex: 935 = 3500K, 90CRI.

<sup>5</sup>See page 4 for actual fixture lengths and mounting locations.











 $<sup>^2\</sup>mbox{BIOS}$  SkyBlue Biological Static & Dynamic page 3.

 $<sup>^{3}\</sup>text{Tunable}$  White, RGB +White and Advanced Color ordering codes page 2.

<sup>\*</sup>DLC options are limited to FL/CA optics, static white 35/40K CCT @ 80CRI, SO lumens, all mounting, all finishes, and all options excluding DIMST.



# **TUNABLE WHITE** - Fixture Level Control





Day-O-Lite offers Tunable White in a range from 2700K-6500K CCT @ 80+CRI and 3SDCM color accuracy for a range of two-channel control options. Consult factory for 90CRI, electrical specifications and other details for each option below.

**2ESN** Option combines tunable white light with a fixture integrated occupancy and daylight harvesting sensor. CCT and intensity is controlled wirelessly with kinetic switches (by Illumra and others). Occupancy and daylight harvesting controlled automatically with parameters configurable with the Philips MasterConnect app available for Android and iPhone smart phones.

#### Applications:

- Spaces occupied overnight (~ 7pm to 7am)
- 24-hour spaces
- Shiftwork & Hospitals
- Senior Living, Alzheimer's Dementia & Assisted Living
- · Higher Education, including student and staff
- Workplace, including areas occupied after 7pm

### Ordering Codes:

2DIM10 = 0-10V

2DMX = DMX

2PSQ = Lutron Athena and Quantum

2CAS = Casambi Wireless

**2ESN** = Philips EasySense

### **RGB + WHITE** - Fixture Level Control









Combine RGB for color effects with LO/SO/HO white CCT's for **general illumination** in a host of applications. All options require DMX control (by others). 80CRI w/3SDCM color accuracy is standard. Consult factory for 90CRI, electrical specifications and other details for each option below. May not be compatible with all fixture variations - consult factory for details when ordering.

#### Applications:

- Entertainment Spaces
- Hospitality & Banquet
- Theatre & Stage
- Seasonal Applications
- Branding
- Wayfinding

### Ordering Codes:

**RGB** = RGB only

**RGB27** = RGB w/2700K

**RGB30** = RGB w/3000K

**RGB35** = RGB W/3500K **RGB40** = RGB w/4000K

**RGB50** = RGB w/5000K

### ADVANCED COLOR - 125mm Pixel Level Control









Day-O-Lite's Advanced Color options combine RGB or RGBW with multi-pixel control for advanced **chases**, animated **visual effects** and other programmable scenes with **125 mm pixel** granularity. Choose from a vibrant color palette with RGB or RGBW LEDs for seamless color mixing and dimming - the perfect replacement for glass neon with improved reliability and durability.

Requires configuration with a remote proprietary digital drive power supply. Auto-addressing makes setup and commissioning quick and easy. DMX (by others) required for control. May not be compatible with all fixture variations - consult factory for details when ordering.

### Applications:

- Architectural Installations
- Digital Signage
- Arcades, Clubs
- Theatre & Stage
- Film & TV sets
- Indoor/Outdoor (IP66)

#### Ordering Codes:

ACRGB = RGB only

AC27 = RGB w/2700 K

**AC30** = RGB w/3000K

AC40 = RGB w/4000 K



# **BIOS SkyBlue**

BIOS SkyBlue biological technology brings the benefits of blue skies inside. BIOS SkyBlue is the only spectrally optimized circadian solution to pinpoint the region that drives wellness benefits including: increased alertness, enhanced productivity, better mood, and better sleep. More information may be found at www.bioslighting.com or by contacting Day-O-Lite directly.

# **BIOS Biological Static** - Daytime Solution

BIOS Biological Static solutions are designed for daytime applications. BIOS Static Biological LED features key BIOS SkyBlue™ (490nm) for maximum daytime circadian impact. BIOS Static Biological LED Light Engines are available in 3000K, 3500K, and 4000K. Lighting controls are easy; simply switch the lights on/off or the lights can be dimmed using a single-channel constant current (CC) LED driver with any standard dimming interface.

#### Applications:


- Spaces occupied during the daytime ~7am 7pm
- K-12 Schools / Higher Education
- Offices
- Daytime Adult Care Facilities
- Medical Offices

BIOS Biological Static Ordering Codes:

**B30** = 3000K

**B35** = 3500K

**B40** = 4000K



# BIOS Biological Dynamic - Day & Night Solution A

BIOS Biological Dynamic solutions are designed to transition from daytime to evening in a dim-to-warm protocol. The daytime CCT includes full BIOS SkyBlue™ (490nm) for maximum daytime circadian impact, while the evening spectrum removes BIOS SkyBlue™ altogether, providing a minimal circadian stimulus after hours. Available in 3000K-2700K, 3500K-3000K and 4000K-3500K. Simply dim the lights in the evening to remove the daytime SkyBlue wavelengths (490nm) and convert your lights from day mode to night mode via a single controller (0-10V, ELV, DMX, Wireless).

# BIOS Biological Tunable White - Day & Night Solution B

BIOS Biological Tunable solutions are designed to transition from daytime to evening in a dim-to-warm protocol. The daytime CCT includes full BIOS SkyBlueTM (490nm) for maximum daytime circadian impact, while the evening spectrum removes BIOS SkyBlueTM altogether, providing a minimal circadian stimulus after hours. Available in 3000K-2700K, 3500K-3000K and 4000K-3500K. Simply dim the lights in the evening to remove the daytime SkyBlue wavelengths (490nm) and convert your lights from day mode to night mode via a single controller (0-10V, ELV, DMX, Wireless).

BIOS Biological Tunable is also compatible with two-channel color tuning systems. Simply dim the lights in the evening to convert your lights from day mode to night mode via a multi-channel controller (0-10V, ELV, DMX, Wireless). 3000K, 3500K and 4000K CCTs all dim to 2700K.

#### Applications:


- Spaces occupied overnight (~ 7pm to 7am)
- 24-hour spaces
- Shiftwork & Hospitals
- Senior Living, Alzheimer's Dementia & Assisted Living
- Higher Education, including student and staff
- Workplace, including areas occupied after 7pm

BIOS Biological
Dynamic White
Ordering Codes:

BIOS Biological
Tunable White
Ordering Codes:

**B30D** = 3000K-2700K **B35D** = 3500K-3000K **B40D** = 4000K-3500K **B40T** = 4000K-2700K **B40T** = 4000K-2700K

### BIOS Biological Dynamic 3500K






#### **Individual Fixtures & Continuous Rows**

	NOMINAL LENGTH				
	4'	3' 8-1/2"	41 1/2"		
ı	6'	7' 5"	86		
ı	8'	11' 1-1/2"	86	44 1/2"	


Individual fixtures and rows are continuously illuminated and joined with included aligner brackets and hardware. Power feed locations and mounting locations are shown below.

Continuous rows longer than 8' and patterns, including EPC/EMC and sensor locations must be approved prior to manufacturing. See below for specifying patterns.



# **Emergency Locations**

EPC will control entire length of individual fixtures. Individual fixtures of differing lengths will deliver the same lumens under EPC power (a 4' fixture will deliver the same total lumens over half the length of an 8' fixture). EMC controlled individual fixtures will deliver lumens per foot as originally specified, unless dimmed at time of power loss. Consult factory for EMC dimming override device.



SENSORS for rows by default will control the feed section (end-left) of the row. Sensors can control more than an 8' section within a row. Consult factory for sensor/section options, or for multiple sensors in a continuous row.




#### Pattern Guide

Profile may be specified in patterns of virtually any configuration. All patterns and corners are continuously illuminated and joined with included aligner brackets and joining hardware. See examples below for suggestions with actual and nominal dimensions. Day-O-Lite's custom manufacturing capabilities allow the specification of custom angled connectors to make non-square patterns possible. (See ILX example below).

All corners and connectors are fully welded to ensure correct dimensions and "square" joinery when assembled.

### **How to Specify**


- 1. Submit your pattern to Day-O-Lite in dimensioned CAD file or submit a fully dimensioned PDF file.
- 2. If EPC/EMC or Sensors are to be included their location needs to be clearly noted.
- 3. Day-O-Lite will design your pattern to as close as is nominally possible given standard LED module lengths, including connectors.
- 4. Day-O-Lite will supply a detailed drawing for approval with final dimensions. All patterns must be approved prior to manufacture.




# O DAY-O-LITE

# **Standard Suspensions**

Standard suspension options include adjustable self-locking aircraft cables (AC) and rigid pendant stems (PD). AC assembly is 48" x 1/16" with a 5" feed canopy and 2" suspension canopies. 60" 18 gauge power and 22 gauge dimming control SJT feed. PD assemblies are 5/8" dia. (or 3/8" IP) hollow stem for power feed by others, 24" is standard. Consult factory for longer suspension lengths and other mounting options.



# **Photometry**




PRFL-24-D-FL-40-LO-4 Flush Lens (FL)

4000K CCT WATTS: 20 LUMENS: 2400 LPW: 120 Distribution: 100% Direct



PRFL-24-D-FL-40-SO-4 **DLC** V5.1 Standard


4000K CCT WATTS: 27 LUMENS: 3200 LPW: 118 Distribution: 100% Direct



PRFL-24-D-FL-40-HO-4 Flush Lens (FL)

4000K CCT WATTS: 34 LUMENS: 4000 LPW: 117 Distribution: 100% Direct


### **Additional Lens Details**



Day-O-Lite, a division of SCW Corporation. All rights reserved. The Day-O-Lite logo is a registered trademark of SCW Corporation. Day-O-Lite reserves the right to change specifications without notice for product improvement.



#### **Additional Lens Details**



# **Specifications**

CONSTRUCTION Extruded aluminum housing. 20 gauge cold rolled steel internal components.

REFLECTOR Die-formed steel finished in highly reflective baked white enamel with pre-finished reflective LED tray.

**OPTICS** LED optimized Satin Ice (SI) acrylic regressed, opal acrylic flush (FL) and opal acrylic drop (DL) lenses are available. Diffuse Polycarbonate (DP) lay-in lens available for matching ARCL-24-D series.

**LED** Static white LED modules in 30/35/40 & 50K CCT, 80/90CRI. Lumen maintenance minimum  $L_{70}$ = 50,000 hours. 3 SDCM color consistency. BIOS SkyBlue, RGB, RGBW and Tunable White options available.

**DRIVER** Standard driver is Class 2 AOC 0-10V to 1%, 120/277V input, PF > 90%, THD < 20 @ 120V. Additional dimming protocols available. All drivers prewired from factory for connection to control system (by others); field replaceable.

**MOUNTING** Standard options include adjustable self-locking aircraft cables (AC), and rigid pendant stems (PD). AC assembly is 48" x 1/16" with a 5" feed canopy and 2" suspension canopies. 18 gauge power and 22 gauge dimming control SJT feed.

FINISH Housing and components finished in baked white enamel. Canopies and pendant stems are white enamel unless otherwise specified.

**CERTIFICATION** Luminaires are cETLus listed conforming to UL STD. 1598 and certified to CSA STD C22.2 NO. 250.0. Suitable for dry & damp locations. Union Made in the United States of America. I.B.E.W. RoHS compliant. DLC V5.1 listed.